

Ceiling Radiation Damper Curtain Type With Insulation Skirt

Application and Design

The CRD-60X, which is manufactured with an attached insulation skirt, has been UL tested and labeled for protection of ceiling openings in fire rated floor/ceiling assemblies with fire resistance ratings of 3 hours or less.

Standard Construction

Frame/Blades: Galvanized steel
(in gauges required
by UL listing R13446).

Fusible Link: Replaceable 165°F (74°C)
UL listed link is standard,
212°F (100°C) is optional.

Finish: Mill galvanized.

Blade Insulation: Non-asbestos UL classified.

Size Limitations

Minimum Size: 6 in. x 4 in.
(152mm x 101mm)

Maximum Size: 24 in. x 24 in.
(610mm x 610mm)

CSFM California State Fire Marshal
Fire Damper Listing (#3226-0981:111)

“UL CLASSIFIED
(see complete marking on product)”

“UL CLASSIFIED to Canadian safety standards
(see complete marking on product)”

Standard 555C (Listing #R13446)

National Fire Protection Association:
NFPA Standards 90A and 101


BOCA, ICBO, SBCCI, & IBC Building Codes

New York City MEA Listing #260-91-M



Thermal Blanket Option

Ceramic fiber or mineral wool thermal blanket available.



*W & H dimensions furnished approximately 1/4 in. (6mm) under size.

Installation instructions available at www.greenheck.com.