



SKU
357159

Job Name:
Mark:
Submitted By:
Date: 06/18/2026

Vari-Green Motor, ZWK601B514016, 0.25 HP, 1 Phase, Product # 357159

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.25 HP	1800	115	50	1	2.85
0.25 HP	1800	220	60	1	1.7
0.25 HP	1800	240	60	1	1.7
0.25 HP	1800	208	50	1	1.7
0.25 HP	1800	240	50	1	1.7
0.25 HP	1800	110	50	1	2.85
0.25 HP	1800	277	50	1	1.5
0.25 HP	1800	230	60	1	1.7
0.25 HP	1800	220	50	1	1.7
0.25 HP	1800	277	60	1	1.5
0.25 HP	1800	230	50	1	1.7
0.25 HP	1800	115	60	1	2.85
0.25 HP	1800	208	60	1	1.7

Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	VN
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	BrushlessDC
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Parcel
Thermal Protection	AutoOverload		

Dimensions

Weight 8.2 lbs