



SKU
320642

Job Name:
Mark:
Submitted By:
Date: 04/11/2026

Motor, Large Frame, 254T, 254Ttgn6531 Mod, Product # 320642

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
15 HP	1800	230	60	3	37.6
15 HP	1800	460	60	3	18.8

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	Yes	Frame Size	254T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight
Thermal Protection	Thermostat		

Dimensions

Shaft Diameter	1.625 in	Weight	325 lbs
-----------------------	----------	---------------	---------