



SKU
317758VA

Job Name:
Mark:
Submitted By:
Date: 04/05/2026

Motor, 215T, 215Tfc6031 Mod, Product # 317758VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
10 HP	1800	575	60	3	10.3

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	CN
Explosion Proof	No	Frame Size	215T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	1.375 in	Weight	177 lbs
-----------------------	----------	---------------	---------