

SKU
310521Job Name:
Mark:
Submitted By:
Date: 06/26/2025

Motor, 0.18Kw, 1500 RPM, 380/400/415V, 50Hz, 3Ph, Product # 310521

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.18 KW	1500	415	50	3	-
0.18 KW	1500	400	50	3	-
0.18 KW	1500	380	50	3	-

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	BR
Explosion Proof	n/a	Frame Size	63
Frame Type	NA	Housing Material	Aluminum
Motor Enclosure	n/a	Motor Insulation	F
Motor Phase	3	Motor Type	IEC
Shipping Type	Freight		

Dimensions

Shaft Diameter	11 in	Weight	25 lbs
----------------	-------	--------	--------

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov