

SKU BSQ-120-10X-3-QD-DR2 Job Name: Mark: Submitted By: Date: 05/04/2025

Square Centrifugal Inline Fan, Product # BSQ-120-10X-3-QD-DR2, 1459-2527 CFM




Model BSQ centrifugal inline fan features a unique combination of installation flexibility, rugged construction, ease of service, high efficiency and low sound levels. These compact fans are the ideal selection for indoor clean air applications including intake, exhaust, return or make-up air.


- 15.875 x 15.875 inch inlet width x height
- 15.875 x 15.875 inch outlet width x height
- Horizontal or vertical mounting

Certifications

AMCA Sound & Air UL/cUL 705



Performance Characteristics



Construction Features

Housing Material	Galvanized Steel							
Drive Type	Belt Drive							
Impeller Type	Centrifugal Wheel							
Impeller Material	Aluminum							
	Motor cover							
Includes	Unassembled drive							
	package							
Certifications	AMCA Sound & Air							
Certifications	UL/cUL 705							
Drive Beekege Description	Motor and drives shipped							
Drive Package Description	loose							

Motor Information

Motor Insulation	F
Motor Phase	3
Motor Type	NEMA
Service Factor	1.15
Voltage	208-230/460
HP	1
Hertz	60
Motor Enclosure	Open Drip Proof
RPM	1800
Nominal Efficiency	83.5
NEMA Frame Size	56

Air and Sound Performance

Motor HP	Max BHP	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625	0.75	0.875	1	1.25	1.5	1.75	2	2.25
1	1.13	2230	1790	CFM	2,527	2,480	2,432	2,384	2,335	2,287	2,238	2,188	2,139	2,034	1,924	1,804	1,662	1,459
				Sones	24	24	24	24	23	22	22	22	22	21	20	19.6	18.7	17.5



- · Greenheck Fan Corporation certifies that the model shown herein is licensed to bear the AMCA Seal. The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- Performance certified is for installation type B: Free inlet, Ducted outlet.
- Power rating (BHP/kW) includes transmission losses.
- Performance ratings do not include the effects of appurtenances (accessories).
- The inlet sound ratings shown are loudness values in fan sones at 5 ft. (1.5 m) in a hemispherical free field calculated per AMCA Standard 301. Values shown are for installation type B: free inlet hemispherical sone levels.

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov

