



SKU
311105

Job Name:
Mark:
Submitted By:
Date: 07/16/2025

Motor, EM3311T-G, 7.5HP, 1800 RPM, 208-230/460V, 60Hz, 3Ph, Product # 311105



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
7.5 HP	1800	230	60	3	19.6
7.5 HP	1800	208	60	3	20.6
7.5 HP	1800	460	60	3	9.8

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	213T
Frame Type	n/a	Housing Material	NA
Motor Enclosure	Open Drip Proof	Motor Insulation	H
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Height	15 in	Length	22 in
Shaft Diameter	1.375 in	Weight	115 lbs
Width	16 in		

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov