



SKU
303041

Job Name:
Mark:
Submitted By:
Date: 06/25/2026

Motor, F0408B2791, 4.6 Watts, 950 RPM, 115V, 60Hz, 1Ph, Product # 303041

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
4.6 W	950	115	60	1	0.62

Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Hertz	60
Housing Material	NA	Motor Enclosure	n/a
Motor Insulation	B	Motor Phase	1
Motor Type	Shaded Pole	Nominal Efficiency	12
Return Eligibility	Non-returnable, customized, or special-order item	RPM	950
Shipping Type	Parcel	Thermal Protection	AutoOverload
Voltage	115		

Dimensions

Weight 3 lbs

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov