



SKU  
312895

Job Name:  
Mark:  
Submitted By:  
Date: 04/04/2026

## Motor, M00218ET3W100L-W22, 2.2 Kw, 3 Phase, Product # 312895

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
2.2 KW	1800	460	60	3	4.05

### Specifications

<b>Base Type</b>	Rigid Base	<b>Country of Origin (Primary)</b>	BR
<b>Explosion Proof</b>	n/a	<b>Frame Size</b>	100
<b>Frame Type</b>	L	<b>Housing Material</b>	Cast Iron
<b>Motor Enclosure</b>	n/a	<b>Motor Insulation</b>	F
<b>Motor Phase</b>	3	<b>Motor Type</b>	IEC
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Freight

### Dimensions

<b>Shaft Diameter</b>	28 in	<b>Weight</b>	74 lbs
-----------------------	-------	---------------	--------

### California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)