



SKU
300871

Job Name:
Mark:
Submitted By:
Date: 06/11/2026

Motor, L3401, 0.167 HP, 1 Phase, Product # 300871

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.167 HP	1200	208	60	1	2.6
0.167 HP	1200	115	60	1	4.6
0.167 HP	1200	230	60	1	2.3

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	48
Frame Type	n/a	Housing Material	NA
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	B
Motor Phase	1	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Parcel

Dimensions

Shaft Diameter	0.5 in	Weight	23 lbs
-----------------------	--------	---------------	--------

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov