



SKU
319706

Job Name:
Mark:
Submitted By:
Date: 06/01/2026

Motor, 056T17W5340 Mod, 0.5HP, 1500 RPM, 208/415V, 50Hz, 3Ph, Product # 319706

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.5 HP	1500	208	50	3	-
0.5 HP	1500	415	50	3	-

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	56
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight
Thermal Protection	Thermostat		

Dimensions

Shaft Diameter	0.625 in	Weight	25 lbs
----------------	----------	--------	--------

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov