



SKU  
306627

Job Name:  
Mark:  
Submitted By:  
Date: 05/18/2026

## Motor, 056C17D5940, 0.5 HP, 1 Phase, Product # 306627



### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.5 HP	1800	115	60	1	8.8
0.5 HP	1800	230	60	1	4.4
0.5 HP	1800	208	60	1	4.2

### Specifications

<b>Base Type</b>	Rigid Base	<b>Country of Origin (Primary)</b>	MX
<b>Explosion Proof</b>	No	<b>Frame Size</b>	56
<b>Frame Type</b>	n/a	<b>Housing Material</b>	Rolled Steel
<b>Motor Enclosure</b>	Open Drip Proof	<b>Motor Insulation</b>	B
<b>Motor Phase</b>	1	<b>Motor Type</b>	NEMA
<b>Return Eligibility</b>	Returnable within 60 days of shipment	<b>Shipping Type</b>	Parcel
<b>Thermal Protection</b>	AutoOverload		

### Dimensions

<b>Shaft Diameter</b>	0.625 in	<b>Weight</b>	24 lbs
-----------------------	----------	---------------	--------

### California Residents

**⚠ WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)