



SKU  
358270VA

Job Name:  
Mark:  
Submitted By:  
Date: 06/26/2025

Motor, Custom, 1/3HP, 1800RPM, 380/400V, 60HZ, 3PH, Product # 358270VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.333 HP	1800	400	60	3	0.6
0.333 HP	1800	380	60	3	0.6

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	56
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	H
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	0.625 in	Weight	35 lbs
----------------	----------	--------	--------