



SKU
312738

Job Name:
Mark:
Submitted By:
Date: 05/04/2026

Motor, 215T, Custom, Product # 312738

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
7.5 HP	1800	380	60	3	-

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	215T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	1.375 in	Weight	225 lbs
-----------------------	----------	---------------	---------