



SKU
328730

Job Name:
Mark:
Submitted By:
Date: 07/06/2025

Motor, Large Frame, 01518Xt3H254T, 15HP, 1800 RPM, 575V, 60Hz, 3Ph, Product # 328730

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
15 HP	1800	575	60	3	13.9

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	BR,MX
Explosion Proof	Yes	Frame Size	254T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight	Thermal Protection	Thermostat

Dimensions

Shaft Diameter	1.625 in	Weight	320 lbs
----------------	----------	--------	---------