



SKU
CSP-A700-VG-QD

Job Name:
Mark:
Submitted By:
Date: 05/30/2026

Inline Cabinet Fan, Product # CSP-A700-VG-QD, 100-801 CFM




Model CSP inline fans are high performance fans designed for exhaust, supply or return air applications where low sound level are required. Units feature an insulated, galvanized steel housing with a forward-curved wheel and an energy efficient, adjustable Vari-Green EC motor.

- 22.625 x 10.5 inch inlet width x height
- 19.5 x 8 inch outlet width x height
- Energy-efficient, speed controllable, Vari-green® motor

Certifications

AMCA Air
UL/cUL 507



A	B	C	D	E	F	G
23.625 in	11.625 in	11.625 in	19.5 in	8 in	22.625 in	10.5 in

Performance Characteristics

No Fan Curve Available.

Construction Features

Housing Material	Galvanized Steel
Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Impeller Material	Polypropylene
Includes	Access Panel Backdraft damper Mounting brackets
Certifications	AMCA Air UL/cUL 507
Speed Controllable	Yes

Motor Information

Motor Insulation	B
Motor Phase	1
Motor Type	BrushlessDC
Motor Enclosure	n/a
Thermal Protection	OneShot

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov