



SKU  
300757

Job Name:  
Mark:  
Submitted By:  
Date: 05/09/2026

**Motor, 7163-6832 Piedras, 13 Watts, 1050|1300|1550 RPM, 115V, 60Hz, 1Ph,  
Product # 300757**



**Performance Characteristics**

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
13 W	1050	115	60	1	0.38
13 W	1550	115	60	1	0.65
13 W	1300	115	60	1	0.5

**Specifications**

<b>Base Type</b>	Extended Thru-Bolt Mount	<b>Country of Origin (Primary)</b>	MX
<b>Explosion Proof</b>	n/a	<b>Frame Size</b>	n/a
<b>Frame Type</b>	n/a	<b>Housing Material</b>	NA
<b>Motor Enclosure</b>	n/a	<b>Motor Insulation</b>	B
<b>Motor Phase</b>	1	<b>Motor Type</b>	Shaded Pole
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Parcel
<b>Thermal Protection</b>	AutoOverload		

**Dimensions**

<b>Height</b>	6 in	<b>Length</b>	4 in
<b>Weight</b>	5 lbs	<b>Width</b>	4 in

**California Residents**

**⚠ WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)