



SKU  
315265

Job Name:  
Mark:  
Submitted By:  
Date: 05/16/2025

## Motor, 00158Ot3E56-S, 1.0|1.5HP, 1500|1800 RPM, 190/380//208-230/460V, 50/60Hz, 3Ph, Product # 315265



### Performance Characteristics

No Fan Curve Available.

### Construction Features

Housing Material	Rolled Steel
Frame Type	n/a

### Motor Information

Motor Insulation	F
Motor Phase	3
Motor Type	NEMA
Service Factor	1.15
Voltage	208-230/460
HP	1 1/2
Hertz	60
Motor Enclosure	Open Drip Proof
RPM	1800
Nominal Efficiency	86.5
NEMA Frame Size	56

### California Residents

#### WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)