



SKU
315265

Job Name:
Mark:
Submitted By:
Date: 06/09/2026

Motor, 00158OT3E56-S, 1.0|1.5 HP, 3 Phase, Product # 315265



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1.5 HP	1800	460	60	3	2.1
1.5 HP	1800	208	60	3	4.64
1 HP	1500	190	50	3	4.6
1.5 HP	1800	230	60	3	4.2
1 HP	1500	380	50	3	2.4

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	BR,MX
Explosion Proof	No	Frame Size	56
Frame Type	n/a	Hertz	60
Housing Material	Rolled Steel	HP	1 1/2
Motor Enclosure	Open Drip Proof	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
NEMA Frame Size	56	Nominal Efficiency	86.5
Return Eligibility	Returnable within 60 days of shipment	RPM	1800
Service Factor	1.15	Shipping Type	Parcel
Voltage	208-230/460		

Dimensions

Height	9 in	Length	17 in
Shaft Diameter	0.625 in	Weight	40 lbs
Width	8 in		

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov