


SKU RBU-2L48-50X-QD Job Name: Mark: Submitted By: Date: 05/03/2025

Axial Upblast Exhaust Fan, Product # RBU-2L48-50X-QD



Model RBU is an upblast axial exhaust fan designed to discharge air and contaminants up and away from the roof deck for commercial and industrial applications like warehouses, manufacturing facilities and distribution centers. Utilizing a welded steel propeller, this belt-driven fan is designed to run at lower RPMs, producing lower sound levels and is recommended for sound sensitive applications. The motor is located inside of the airstream and is cooled as air exhausts over the motor.

- 48 inch steeply pitched, fabricated steel propeller for low sound levels
- 58 x 58 inch base with prepunched mounting holes for easy attachment to roof curb
- 54.5 x 54.5 inch recommended roof opening




Α	В	С	D	Е	F	G
58 in	40 in	19.375	1.75 in	52.75 in	11.75 in	56 in

Certifications

AMCA Sound & Air UL/cUL 705

Performance Characteristics



Construction Features

Housing Material	Galvanized Steel			
Drive Type	Belt Drive			
Impeller Type	Propeller			
Impeller Material	Steel			
Includes	Steel butterfly damper			
Certifications	AMCA Sound & Air UL/cUL 705			
Drive Package Description	Drives Assembled			
Required Accessory	Roof curb for new installations			

Air and Sound Performance

Motor HP	Max BHP	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625
5 5.00	559	0	CFM	-	-	-	-	-	-	
			Sones	-	-	-	-	-	-	
5 5.62	F 00	2 582	494	CFM	37,220	35,349	32,956	29,829	27,259	20,547
	5.62			Sones	30	30	30	30	30	30

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov

