



SKU
312384VA

Job Name:
Mark:
Submitted By:
Date: 08/02/2025

Motor, 182T, 182Tffcd6026 Mod, Product # 312384VA

Performance Characteristics

| Power | Speed | Voltage | Frequency | Phase | Full Load Amp Draw |
|-------|-------|---------|-----------|-------|--------------------|
| 3 HP | 1800 | 230 | 60 | 3 | 7.8 |

Specifications

| | | | |
|-----------------|---------------------------|-----------------------------|-----------|
| Base Type | Rigid Base | Country of Origin (Primary) | MX |
| Explosion Proof | No | Frame Size | 182T |
| Frame Type | n/a | Housing Material | Cast Iron |
| Motor Enclosure | Totally Enclosed Air Over | Motor Insulation | F |
| Motor Phase | 3 | Motor Type | NEMA |
| Shipping Type | Freight | | |

Dimensions

| | | | |
|----------------|----------|--------|--------|
| Shaft Diameter | 1.125 in | Weight | 99 lbs |
|----------------|----------|--------|--------|