



SKU
300520

Job Name:
Mark:
Submitted By:
Date: 10/26/2025

Motor, 5KH37PN33X, 0.1|0.25 HP, 1 Phase, Product # 300520



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.25 HP	1800	115	60	1	4.2
0.1 HP	1200	115	60	1	2.7

Specifications

Base Type	Resilient Base	Country of Origin (Primary)	MX
Explosion Proof	No	Frame Size	48
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Open Drip Proof	Motor Insulation	B
Motor Phase	1	Motor Type	NEMA
Shipping Type	Parcel	Thermal Protection	AutoOverload

Dimensions

Height	9 in	Length	14 in
Shaft Diameter	0.5 in	Weight	21 lbs
Width	8 in		

California Residents

 WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov