



SKU
315222

Job Name:
Mark:
Submitted By:
Date: 04/04/2026

Motor, 37A001-0137G2, 1.5HP, 720 RPM, 230/460V, 60Hz, 3Ph, Product # 315222

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1.5 HP	720	460	60	3	3.9
1.5 HP	720	230	60	3	7.8

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	213T
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	1.375 in	Weight	102 lbs
-----------------------	----------	---------------	---------

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov