



SKU
311622

Job Name:
Mark:
Submitted By:
Date: 05/11/2026

Motor, 00318XT3E182T, 3 HP, 3 Phase, Product # 311622

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
3 HP	1800	230	60	3	8.02
3 HP	1500	380	50	3	4.72
3 HP	1800	208	60	3	8.65
3 HP	1800	460	60	3	4.01

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	BR
Explosion Proof	Yes	Frame Size	182T
Frame Type	n/a	Hertz	60
Housing Material	Cast Iron	HP	3
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
NEMA Frame Size	182T	Nominal Efficiency	89.5
Return Eligibility	Returnable within 60 days of shipment	RPM	1800
Service Factor	1.15	Shipping Type	Freight
Thermal Protection	Thermostat	Voltage	208-230/460

Dimensions

Shaft Diameter	1.125 in	Weight	127 lbs
-----------------------	----------	---------------	---------

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov