



SKU
301330

Job Name:
Mark:
Submitted By:
Date: 04/03/2026

Motor, Large Frame, 5HP, 900 RPM, 208-230/460V, 60Hz, 3Ph, Product # 301330

Performance Characteristics

| Power | Speed | Voltage | Frequency | Phase | Full Load Amp Draw |
|-------|-------|---------|-----------|-------|--------------------|
| 5 HP | 900 | 230 | 60 | 3 | 16 |
| 5 HP | 900 | 208 | 60 | 3 | 16.2 |
| 5 HP | 900 | 460 | 60 | 3 | 8 |

Specifications

| | | | |
|---------------------------|---|------------------------------------|--------------|
| Base Type | Rigid Base | Country of Origin (Primary) | US |
| Explosion Proof | No | Frame Size | 254T |
| Frame Type | n/a | Housing Material | Rolled Steel |
| Motor Enclosure | Open Drip Proof | Motor Insulation | F |
| Motor Phase | 3 | Motor Type | NEMA |
| Return Eligibility | Non-returnable, customized, or special-order item | Shipping Type | Freight |

Dimensions

| | | | |
|-----------------------|----------|---------------|---------|
| Shaft Diameter | 1.625 in | Weight | 220 lbs |
|-----------------------|----------|---------------|---------|

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov