



SKU
311433

Job Name:
Mark:
Submitted By:
Date: 05/02/2026

Motor, 00218ET3W100L-W22, 2.2 Kw, 3 Phase, Product # 311433

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
2.2 KW	1500	240	50	3	-
2.2 KW	1500	400	50	3	4.05
2.2 KW	1800	460	60	3	4.05
2.2 KW	1500	380	50	3	-
2.2 KW	1500	220	50	3	-
2.2 KW	1500	415	50	3	4.05

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	BR
Explosion Proof	n/a	Frame Size	100
Frame Type	L	Housing Material	Cast Iron
Motor Enclosure	n/a	Motor Insulation	F
Motor Phase	3	Motor Type	IEC
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	28 in	Weight	102 lbs
----------------	-------	--------	---------

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov