

SKU
308140Job Name:
Mark:
Submitted By:
Date: 12/14/2025

Motor, L3510, 1 HP, 1 Phase, Product # 308140

Performance Characteristics



Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1 HP	1800	230	60	1	7
1 HP	1800	115	60	1	13
1 HP	1800	208	60	1	7

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	56
Frame Type	n/a	Housing Material	NA
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	B
Motor Phase	1	Motor Type	NEMA
Return Eligibility	Returnable within 60 days of shipment	Shipping Type	Parcel

Dimensions

Height	11 in	Length	16 in
Shaft Diameter	0.625 in	Weight	41 lbs
Width	12 in		

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov