

SKU 305281

Job Name: Mark: Submitted By: Date: 08/02/2025

Motor, 4.4|10HP, 1000|1500 RPM, 190V, 50Hz, 3Ph, Product # 305281

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
4.4 HP	1000	190	50	3	-
10 HP	1500	190	50	3	-

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	284T
Frame Type	n/a	Housing Material	NA
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter Weight 485 lbs 1.875 in

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov