



SKU
312940

Job Name:
Mark:
Submitted By:
Date: 05/15/2025

Motor, 56H11O15504, 1.5|2HP, 1000|1200 RPM, 190/380//208-230/460V, 50/60Hz, 3Ph, Product # 312940



Performance Characteristics

No Fan Curve Available.

Construction Features

Housing Material	Rolled Steel
Frame Type	n/a

Motor Information

Motor Insulation	B
Motor Phase	3
Motor Type	NEMA
Motor Enclosure	Open Drip Proof

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov