



SKU  
301230

Job Name:  
Mark:  
Submitted By:  
Date: 04/02/2026

**Motor, 110423, 0.333HP, 1500 RPM, 110/220V, 50Hz, 1Ph, Product # 301230**

**Performance Characteristics**

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.333 HP	1500	110	50	1	7
0.333 HP	1500	220	50	1	3.5

**Specifications**

<b>Base Type</b>	Rigid Base	<b>Country of Origin (Primary)</b>	US
<b>Explosion Proof</b>	No	<b>Frame Size</b>	56
<b>Frame Type</b>	n/a	<b>Housing Material</b>	NA
<b>Motor Enclosure</b>	Totally Enclosed Fan Cooled	<b>Motor Insulation</b>	B
<b>Motor Phase</b>	1	<b>Motor Type</b>	NEMA
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Parcel

**Dimensions**

<b>Shaft Diameter</b>	0.625 in	<b>Weight</b>	25 lbs
-----------------------	----------	---------------	--------

**California Residents**

**⚠ WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)