



SKU  
357158

Job Name:  
Mark:  
Submitted By:  
Date: 04/15/2026

## Vari-Green Motor, ZWK601B514015, 0.167 HP, 1 Phase, Product # 357158

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.167 HP	1800	230	50	1	1.3
0.167 HP	1800	277	60	1	1.1
0.167 HP	1800	208	60	1	1.3
0.167 HP	1800	110	50	1	2.2
0.167 HP	1800	277	50	1	1.1
0.167 HP	1800	115	60	1	2.2
0.167 HP	1800	220	50	1	1.3
0.167 HP	1800	115	50	1	2.2
0.167 HP	1800	240	50	1	1.3
0.167 HP	1800	208	50	1	1.3
0.167 HP	1800	230	60	1	1.3

### Specifications

<b>Base Type</b>	Extended Thru-Bolt Mount	<b>Country of Origin (Primary)</b>	VN
<b>Explosion Proof</b>	n/a	<b>Frame Size</b>	n/a
<b>Frame Type</b>	n/a	<b>Housing Material</b>	NA
<b>Motor Enclosure</b>	n/a	<b>Motor Insulation</b>	B
<b>Motor Phase</b>	1	<b>Motor Type</b>	BrushlessDC
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Parcel
<b>Thermal Protection</b>	AutoOverload		

### Dimensions

**Weight** 8.2 lbs