



SKU
358629

Job Name:
Mark:
Submitted By:
Date: 05/08/2026

Motor, Large Frame, 10-0000-2520, 15 HP, 3 Phase, Product # 358629

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
15 HP	1200	460	60	3	19.4

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	284T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	1.875 in	Weight	437 lbs
-----------------------	----------	---------------	---------