



SKU
358592

Job Name:
Mark:
Submitted By:
Date: 08/02/2025

Motor, Large Frame, Ht075504Npw22, 0.85HP, 1800 RPM, 575V, 60Hz, 3Ph, Product # 358592

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.85 HP	1800	575	60	3	67.3

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	BR
Explosion Proof	No	Frame Size	365T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	2.375 in	Weight	0 lbs
----------------	----------	--------	-------