



SKU  
308318

Job Name:  
Mark:  
Submitted By:  
Date: 10/15/2025

## Motor, A0820B3680, 139.9 Watts, 1050|1300|1550 RPM, 115V, 60 Hz, 1 Phase, Product # 308318



### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
139.9 W	1550	115	60	1	2.6
139.9 W	1300	115	60	1	2.6
139.9 W	1050	115	60	1	2

### Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Hertz	60
Housing Material	NA	HP	1/8
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	PSC
Nominal Efficiency	50	RPM	1550
Service Factor	1	Shipping Type	Parcel
Thermal Protection	AutoOverload	Voltage	115
Watts	139.9		

### Dimensions

Height	10 in	Length	11 in
Weight	8 lbs	Width	11 in

### California Residents

#### WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)