



SKU
356506VK

Job Name:
Mark:
Submitted By:
Date: 08/02/2025

Motor, 35-0000-0631, 0.75HP, 1800RPM, 575V, 60HZ, 3PH, Product # 356506VK

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.75 HP	1800	575	60	3	1.1

Specifications

Base Type	C-Face Footed	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	56C
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Parcel		

Dimensions

Shaft Diameter	0.625 in	Weight	37 lbs
----------------	----------	--------	--------