



SKU  
358815

Job Name:  
Mark:  
Submitted By:  
Date: 07/06/2025

Motor, EM3218T-BG, 5HP, 1800RPM, 208/230/460V, 60HZ, 3PH, Product # 358815

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
5 HP	1800	230	60	3	13.2
5 HP	1800	460	60	3	6.6
5 HP	1800	208	60	3	14

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	184T
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Open Drip Proof	Motor Insulation	H
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	1.125 in	Weight	83 lbs
----------------	----------	--------	--------