



SKU
358829

Job Name:
Mark:
Submitted By:
Date: 05/16/2026

Motor, 00212ET3E184T-W22, 2 HP, 3 Phase, Product # 358829

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
2 HP	1200	208	60	3	7.13
2 HP	1200	230	60	3	6.44
2 HP	1200	460	60	3	3.22

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	BR
Explosion Proof	No	Frame Size	184T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	1.125 in	Weight	99 lbs
-----------------------	----------	---------------	--------