



SKU
358864

Job Name:
Mark:
Submitted By:
Date: 07/22/2025

Motor, Custom, 0.37KW, 1500RPM, 400V, 50HZ, 3PH, Product # 358864

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.37 KW	1500	400	50	3	0.9

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	FI
Explosion Proof	n/a	Frame Size	71
Frame Type	NA	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	H
Motor Phase	3	Motor Type	IEC
Shipping Type	Parcel	Thermal Protection	Thermistors

Dimensions

Shaft Diameter	14 in	Weight	33 lbs
----------------	-------	--------	--------