



SKU
358900

Job Name:
Mark:
Submitted By:
Date: 04/07/2026

Motor, CXL050742A-50, 0.75 HP, 1 Phase, Product # 358900

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.75 HP	1500	220	50	1	4.8
0.75 HP	1500	110	50	1	9.6

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	Yes	Frame Size	56C
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	B
Motor Phase	1	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Parcel
Thermal Protection	Thermostat		

Dimensions

Shaft Diameter	0.625 in	Weight	50.8 lbs
----------------	----------	--------	----------