



SKU  
358989

Job Name:  
Mark:  
Submitted By:  
Date: 06/02/2026

## Motor, 00136ET3H143T-S, 1 HP, 3 Phase, Product # 358989

### Performance Characteristics

| Power | Speed | Voltage | Frequency | Phase | Full Load Amp Draw |
|-------|-------|---------|-----------|-------|--------------------|
| 1 HP  | 3600  | 575     | 60        | 3     | 1.15               |

### Specifications

|                           |   |                                    |              |
|---------------------------|---|------------------------------------|--------------|
| <b>Base Type</b>          | Rigid Base  | <b>Country of Origin (Primary)</b> | MX           |
| <b>Explosion Proof</b>    | No  | <b>Frame Size</b>                  | 143T         |
| <b>Frame Type</b>         | n/a   | <b>Housing Material</b>            | Rolled Steel |
| <b>Motor Enclosure</b>    | Totally Enclosed Fan Cooled                       | <b>Motor Insulation</b>            | F            |
| <b>Motor Phase</b>        | 3   | <b>Motor Type</b>                  | NEMA         |
| <b>Return Eligibility</b> | Non-returnable, customized, or special-order item | <b>Shipping Type</b>               | Parcel       |

### Dimensions

|                       |          |               |          |
|-----------------------|----------|---------------|----------|
| <b>Shaft Diameter</b> | 0.875 in | <b>Weight</b> | 26.3 lbs |
|-----------------------|----------|---------------|----------|