



SKU
358989

Job Name:
Mark:
Submitted By:
Date: 05/10/2026

Motor, 00136ET3H143T-S, 1 HP, 3 Phase, Product # 358989

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1 HP	3600	575	60	3	1.15

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	MX
Explosion Proof	No	Frame Size	143T
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Parcel

Dimensions

Shaft Diameter	0.875 in	Weight	26.3 lbs
-----------------------	----------	---------------	----------