



SKU
311392VA

Job Name:
Mark:
Submitted By:
Date: 06/28/2025

Motor, 5HP, 1000 RPM, 380V, 50Hz, 3Ph, Product # 311392VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
5 HP	1000	380	50	3	-

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	254T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	H
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight	Thermal Protection	Thermostat

Dimensions

Shaft Diameter	1.625 in	Weight	660 lbs
----------------	----------	--------	---------

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov