



SKU
1039377

Job Name:
Mark:
Submitted By:
Date: 06/28/2025

Motor, CUSTOM, 1.5HP, 1800 RPM, 380V, 60Hz, 3Ph, Product # 1039377

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1.5 HP	1800	380	60	3	2.8

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	Yes	Frame Size	145T
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Parcel	Thermal Protection	Thermostat

Dimensions

Shaft Diameter	0 in	Weight	50 lbs
----------------	------	--------	--------