



SKU
1043774

Job Name:
Mark:
Submitted By:
Date: 08/02/2025

Motor, Custom, 5HP, 1800 RPM, 460V, 60HZ, 3 PH, Product # 1043774

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
5 HP	1800	460	60	3	6.5

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	184T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	1.125 in	Weight	115 lbs
----------------	----------	--------	---------