



SKU
1044455

Job Name:
Mark:
Submitted By:
Date: 05/01/2026

Motor, Large Frame, CEM2334T, 20 HP, 3 Phase, Product # 1044455

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
20 HP	1800	460	60	3	24
20 HP	1800	208	60	3	52
20 HP	1800	230	60	3	48

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	256TC
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	1.625 in	Weight	298 lbs
-----------------------	----------	---------------	---------