



SKU  
1043237

Job Name:  
Mark:  
Submitted By:  
Date: 04/07/2026

## Motor, 07C151T461G1, 5 HP, 3 Phase, Product # 1043237

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
5 HP	1200	230	60	3	14
5 HP	1200	460	60	3	7
5 HP	1200	208	60	3	15.4

### Specifications

<b>Base Type</b>	Rigid Base	<b>Country of Origin (Primary)</b>	US
<b>Explosion Proof</b>	No	<b>Frame Size</b>	215T
<b>Frame Type</b>	n/a	<b>Housing Material</b>	Cast Iron
<b>Motor Enclosure</b>	Totally Enclosed Fan Cooled	<b>Motor Insulation</b>	F
<b>Motor Phase</b>	3	<b>Motor Type</b>	NEMA
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Freight
<b>Thermal Protection</b>	Thermostat		

### Dimensions

<b>Shaft Diameter</b>	1.375 in	<b>Weight</b>	226 lbs
-----------------------	----------	---------------	---------