



SKU  
1043274

Job Name:  
Mark:  
Submitted By:  
Date: 04/01/2026

## Motor, YHS80-30-D1.5, 16.7 Watts, 1 Phase, Product # 1043274



### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
16.7 W	900	115	60	1	0.17

### Specifications

<b>Base Type</b>	Yoke Mount	<b>Country of Origin (Primary)</b>	CN
<b>Explosion Proof</b>	n/a	<b>Frame Size</b>	n/a
<b>Frame Type</b>	n/a	<b>Housing Material</b>	Rolled Steel
<b>Motor Enclosure</b>	n/a	<b>Motor Insulation</b>	A
<b>Motor Phase</b>	1	<b>Motor Type</b>	PSC
<b>Return Eligibility</b>	Returnable within 60 days of shipment	<b>Shipping Type</b>	Parcel
<b>Thermal Protection</b>	Dual		

### Dimensions

**Weight** 3 lbs