



SKU  
356907

Job Name:  
Mark:  
Submitted By:  
Date: 07/05/2025

Motor, Large Frame, 09-0000-2764, 20 HP, 3000 RPM, 400V, 50HZ, 3PH, Product # 356907

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
20 HP	3000	400	50	3	26

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	256T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	1.625 in	Weight	322 lbs
----------------	----------	--------	---------