



SKU
357402

Job Name:
Mark:
Submitted By:
Date: 08/02/2025

Motor, Large Frame, XM282542T, 20 HP/25 HP,
1500/1800RPM190/380V|230/460V50/60HZ, 3PH, Product # 357402

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
20 HP	1500	380	50	3	30
20 HP	1500	190	50	3	60
25 HP	1800	460	60	3	31
25 HP	1800	230	60	3	62

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	Yes	Frame Size	284T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight	Thermal Protection	Thermostat

Dimensions

Shaft Diameter	1.875 in	Weight	537 lbs
----------------	----------	--------	---------