



SKU
1039438

Job Name:
Mark:
Submitted By:
Date: 04/07/2026

Motor, S33G352ZB-08F, 18 Watts, 1 Phase, Product # 1039438



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
18 W	1050	115	60	1	1.8

Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	CN
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Hertz	60
Housing Material	NA	Motor Enclosure	n/a
Motor Insulation	B	Motor Phase	1
Motor Type	Shaded Pole	Nominal Efficiency	15
Return Eligibility	Returnable within 60 days of shipment	RPM	1050
Service Factor	1	Shipping Type	Parcel
Thermal Protection	Dual	Voltage	115
Watts	19.2		

Dimensions

Height	10 in	Length	11 in
Weight	4 lbs	Width	11 in

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov